

FLOW

CFM

5 - - - - -


10 - - - - -

15 - - - - -


20 - - - - -

25 - - - - -


20° CONE



GAP - 1/4"



3/8"




1/2"

ENLARGED 2.56X

**FLOW
CFM**

10 ———
15 ———
20 ———

**10° CONE WITH 1" PROBE
AND GLANS**



GAP - 1/4"

3/8"

1/2"

AT INLET

ENLARGED 2.6X




**FLOW
CFM**

10 

15 

20 

**20° CONE WITH 1" PROBE
AND GLANS**



GAP - 1/4"

3/8"

1/2"

ENLARGED 2.6X